

HONEYWELL
PART NUMBER

V7-3E14E7-000-1

CWB8390

SUPERCEDES
X200836-V7

REV	DOCUMENT	CHANGED BY	CHECK
A	0035319	JA 16NOV07	ASD

CHARACTERISTICS

OPERATING FORCE -----50 GRAM MAX
 RELEASE FORCE ----- 5 GRAM MIN
 DIFFERENTIAL TRAVEL ---.002-.010
 OVERTRAVEL ----- .050 MIN
 FREE POSITION ----- .625 MAX



ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

L216

10A-1/3 HP-125, 250, 277 VAC
 1/2A-125 VDC ; 1/4A-250 VDC
 4A-125 VAC "L"




NOTE:
 1 - ALLIANCE PART NUMBER "RSPC 70411901" MARKED ON SWITCH

PRODUCT CODE: CWB8390

DESIGN UNITS: INCH
 TOLERANCES UNLESS NOTED:

NO PLACE	X	±	0.040
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	0.0005
ANGLES		±	2

THIRD ANGLE PROJECTION



DRAWN JA 16NOV07
 CHECK ASD 16NOV07

THIS DRAWING COVERS A PROPRIETARY ITEM
 AND IS THE PROPERTY OF HONEYWELL.
 THIS DRAWING IS NOT TO BE COPIED OR USED
 WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
 OTHER HONEYWELL ENGINEERING
 STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
A	I	V7-3E14E7-000-1	A
SCALE	-	SHEET 1 OF 1	