




NOTE -
△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ——— 22-28 OZ
RELEASE FORCE ——— 4 OZ MIN
DIFFERENTIAL TRAVEL ——— .0025-.0050
OVERTRAVEL ——— .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

UNDERWRITERS' LAB. INC. LISTED RATING
⑧ - L96- 15 A-125, 250, OR 480 VAC
1/2 A-125 VDC; 1/4 A-250 VDC
1/8 HP-125 VAC; 1/4 HP-250 VAC



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .060 LB

BZ-R31

M

DRAWING NUMBER

ISSUE

REVISIONS

A	CO 15200	H B W	3 FEB 64
B	CO 19782	M B F	30 DEC 64
C	CO 20409	Q M W	30 JUL 65
D	CO 20463	W E G	11 AUG 65
E	CO 48767	Y M M	7 JAN 81
F	CO 69351	J W B	16 JUL 91
G	CO 77589	K D R	29 MAR 94

FO-50378

DRAWN

H B W

3 FEB 64

CHECK

LS D

14 FEB 64

REPLACES

RELEASE NO.

CHECK