



THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT

| LOC | DIST | REVISIONS |     |                           | DATE    | DWN | APVD |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| J   | —    | P         | LTR | DESCRIPTION               |         |     |      |
|     |      | D2        |     | REVISED PER ECO-11-005030 | 22MAR11 | RK  | HMR  |



1. 材質: SS-108 (一般)
2. 一般公差:  $\pm 0.5$
3. 適用製品規格は無し

A - A

△ 品川商工発行のカタログと本図で寸法を優先する。

法が異なる場合は

1. MATERIAL: SS-108 (GENERAL)
  2. GENERAL TOLERANCE:  $\pm 0.5$
  3. APPLICABLE PRODUCT SPEC NOT AVAILABLE
- △ IN THE EVENT OF CONFLICT BETWEEN THE REQUIREMENTS OF THIS CUSTOMER DRAWING AND THE SHINAGAWA SHOKO CO LTD CATALOG THIS CUSTOMER DRAWING SHALL TAKE PRECEDENCE

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ OBSOLETE

|            |            |
|------------|------------|
| X-170892-X | SEE 170892 |
| X-170893-X | SEE 170893 |
| X-170889-X | SEE 170889 |
| X-170888-X | SEE 170888 |
| X-170890-X | SEE 170890 |
| X-170891-X | SEE 170891 |
| X-170823-X | SEE 170823 |
| PN         | REMARK     |

|       |    |    |      |      |     |         |                       |                     |
|-------|----|----|------|------|-----|---------|-----------------------|---------------------|
| CLEAR | 14 | 7  | 4.5  | 1.5  | 0.6 | 5.9     | 224215                | <del>170887-5</del> |
|       | 13 | 6  |      | 3.5  | 0.7 |         | 224235                | 170887-4            |
|       | 14 | 7  |      | 3.2  |     |         | 224232                | 170887-3            |
| BLACK | 13 | 6  | 4    | 2.5  | 5.4 | 224225B | 170887-2              |                     |
| CLEAR |    |    |      |      |     | 224225  | 170887-1              |                     |
| COLOR | L  | L1 | φ D2 | φ D1 | T   | H       | SHINAGAWA<br>SHOKO PN | PN                  |

|                       |                        |
|-----------------------|------------------------|
| WIRE RANGE<br>抱合電線断面積 | INSULATION DIA<br>被覆外径 |
|-----------------------|------------------------|

|                                                     |  |                                                        |                    |                              |                    |  |
|-----------------------------------------------------|--|--------------------------------------------------------|--------------------|------------------------------|--------------------|--|
| DIMENSIONS:<br>単位: 耗<br>MM                          |  | DWN<br>A.YAMAGUCHI<br>31 AUG 00                        | MATERIAL<br>材料     |                              | FINISH<br>仕上       |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>一般公差   |  | CHK<br>D.MATSUURA<br>31 AUG 00                         |                    |                              |                    |  |
| 0 PLC<br>1 PLC<br>2 PLC<br>3 PLC<br>4 PLC<br>ANGLES |  | APVD<br>K.BETSUI<br>31 AUG 00                          |                    |                              |                    |  |
| PRODUCT SPEC<br>製品規格                                |  | NAME<br>名称                                             |                    |                              |                    |  |
| APPLICATION SPEC<br>取付適用規格                          |  | CONNECT SLEEVE FOR<br>5DIA SERIES SHUR PLUG RECEPTACLE |                    |                              |                    |  |
| WEIGHT                                              |  | SIZE<br>A4                                             | CAGE CODE<br>00779 | DRAWING NO<br>番号<br>C-170887 | RESTRICTED TO<br>— |  |
| CUSTOMER DRAWING                                    |  |                                                        | SCALE<br>尺度<br>4:1 | SHEET<br>1 OF 1              | REV<br>D2          |  |