

4-Port USB-C Hub, USB-C to 4x USB-A Ports, USB 3.0, Silver

MODEL NUMBER: **U460-004-4A**



Adds USB-A ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U460-004-4A USB 3.1 Gen 1 USB-C Portable Hub expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals and charging mobile devices—all at the same time.

The plug-and-play U460-004-4A requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer. Each port supports up to 5V/1.5A (7.5W) for fast charging of mobile devices. They also support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

A USB Micro-B port connects to an optional external USB power adapter to provide the hub with additional power if needed.

Features

Turn Your Device's USB-C Port into a Workstation

- Ideal for adding USB peripherals and powering and charging a mobile device simultaneously
- Plug-and-play operation with no software, drivers or external power required
- Lightweight aluminum housing about the size of a credit card for easy carrying in a pocket, purse or laptop bag

Connect USB Peripherals

- 4 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals
- Supports up to 5V/1.5A (7.5W) for fast charging of mobile devices
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.1

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-A ports provide up to 1.5A each for charging devices
- USB Micro-B port connects to optional adapter for extra power
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port

Package Includes

- U460-004-4A USB 3.1 Gen 1 USB-C Portable Hub



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Note: Host must support USB OTG (On-the-Go)

Extra Port for Extra Power

- USB Micro-B port connects to optional external power adapter to provide hub with additional power if needed

Built-In Cable with Reversible USB-C Connector

- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Specifications

OVERVIEW	
UPC Code	037332190208
Product Type	Hub
Technology	USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Detail	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Bus Powered	Yes
Product Length (in.)	14.4
Product Length (cm.)	36.58
Product Length (ft.)	1.2
Product Length (m.)	0.37
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
CHARGING	
Charging Ports / Amps	(4) 1.5A
Charging Ports	USB-A: 5V 1.5A (7.5W)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Total Charging Watts	7.5
PHYSICAL	
Color	Silver
Cable Jacket Rating	VW-1
Material of Construction	Aluminum
Shipping Dimensions (hwd / cm)	3.05 x 12.45 x 9.91
Shipping Dimensions (hwd / in.)	1.20 x 4.90 x 3.90
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.22
Unit Dimensions (hwd / in.)	0.6 x 2.8 x 2.6
Unit Packaging Type	Box
Unit Weight (kg)	0.07
Unit Weight (lbs.)	0.16
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 °F (0 to 50 °C)
Storage Temperature Range	14 to 167 °F (-10 to 75 °C)
Relative Humidity	0% to 85% RH, Non-Condensing
BTUs	2.4 BTU/Hr
Power Consumption (Watts)	0.7
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port
CONNECTIONS	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Side B - Connector 2	MICRO-USB B (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>