

Home > Industrial Products > Switches > Pendant Switches (Cord/ Nurse Call)

PENDANT NURSE CALL CORD SWITCHES



Momentary cord (pendant) switches can be specified with red or black pushbuttons, 1-C switching, solder terminals and metal handle (Series E900), plastic handle (Series EP900), or metal handle with clamp and strain relief (Series ED900).



ED900S Sealed Series

Waterproof and Dustproof to IP67,
Thermoplastic Rubber Flex Relief



ED900 Die-cast Series

Features Cable Clamp and Thermoplastic
Rubber Flex Relief



E900 Copper Series

Basic Field Installable Switch with Nickel
Plated Copper Housing



EP900 Plastic Series

Basic Switch Field Installable Switch with
Cost Effective Plastic Design



E921 Ergonomic Series

Easy to Grip with Tactile Feedback. Double-
redundant Circuitry. Pre-installed on 6' Cable



921 Cordette® Series

Available with Phono Jack or Pre-installed on
6' Cable. Many Custom Options Available,
including ST901F Sealed Flex Relief.

Questions? Contact Switchcraft Customer Support at 1-773-792-2700

Product	Description	
EP913DS14		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.140" (3.6mm), "D" Circuit
EP913DS17		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.170" (4.31mm), "D" Circuit
EP913DS20		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.200" (5mm), "D" Circuit



BUY IN STOCK



BUY IN STOCK



BUY IN STOCK

Downloads:

Specification Sheet

Product Bulletin

Associated Products:



Open Frame Rear Mount Switch

EP913DS23		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.230" (5.8mm), "D" Circuit	 	BUY	IN STOCK
EP913S14		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.140" (3.6mm)	 	BUY	IN STOCK
EP913S17		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.170" (4.31mm)	 	BUY	IN STOCK
EP913S20		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.200" (5mm)	 	BUY	IN STOCK
EP913S23		Sealed Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.230" (5.8mm)	 	BUY	IN STOCK
ED903		Momentary Cord Switch, solder terminals, metal handle with clamp and strain relief, red pushbutton, Max. Cable OD 0.375" (9.5mm)	 	BUY	IN STOCK
ED913		Momentary Cord Switch, solder terminals, metal handle with clamp and strain relief, black pushbutton, Max. Cable OD 0.375" (9.5mm)	 	BUY	IN STOCK
E903		Momentary Cord Switch, solder terminals, metal handle, red pushbutton, Max. Cable OD 0.375" (9.5mm)		BUY	IN STOCK
E913		Momentary Cord Switch, solder terminals, metal handle, black pushbutton, Max. Cable OD 0.375" (9.5mm)		BUY	IN STOCK
EP903		Momentary Cord Switch, solder terminals, plastic handle, red pushbutton, Max. Cable OD 0.250" (6.4 mm)		BUY	IN STOCK
EP913		Momentary Cord Switch, solder terminals, plastic handle, black pushbutton, Max. Cable OD 0.250" (6.4 mm)		BUY	IN STOCK
E921KA		Ergonomic pendant switch, 6ft cable, strip and tin leads, "A" circuit.		BUY	IN STOCK
E921KC		Ergonomic pendant switch, 6ft cable, strip and tin leads, "C" circuit.		BUY	IN STOCK
921KX		Cordette Switch, phone jack termination plus 6-foot, 2 conductor cable with stripped and tinned leads.	 	BUY	IN STOCK
921X		Cordette switch, phono jack termination.		BUY	IN STOCK



Rear (0.250 mounting hole) and Front (0.469 mounting hole) Pushbutton Switches



Round Pushbutton Switch PC Mount



PENDANT (NURSE CALL)



950, 960 Series, Rear Mount, .250 Mounting Hole



Momentary Sealed Button Switch