

Product Search

Product Catalog

[Products](#)

[Lamps & LED-Lamps](#)

[Incandescent lamps](#)

[Miniatur Lamps](#)

Markets

[Automotive](#)

[Aviation](#)

[Gaming](#)

[Illumination](#)

[Transport](#)

[Custom Projects](#)

POS-CCE - Romania Sibiu



Product details

Article: 02112520





Lamp, T5, Wedge Base, 24V, 40mA

Description

Designation: Lamp, T5, Wedge Base, 24V, 40mA

International Number: HR85

Average Lifetime AC: 5000 h

Electrical features

Voltage: 24 V

Current: 40 mA

Mechanical features

Socket: WB (W2x4,6d)

Lamp size: T-1 1/2

Diameter: 5 mm

Gallery





Click on a small picture to select it. Click the large image to view full size.



Multivoltage LED Lamps
Covering the voltage range of 6 to 32V
Available in all colours and BA9s socket



Stock inquiry

Latest News

2014-08-28
New CML catalogue: "CML LED lamps for signalisation and LED panel mount indicators"
>> [More details](#)

2014-07-07
Optimized BA15d LED lamp for use in light towers
>> [More details](#)

2013-11-10
StockCheck function added to the website
>> [More details](#)