



Part Number : [1300960063](#)

Product Description : Safeway Wire Mesh Grip,
Straight Male, Cable Diameter 20.83-25.40mm
(.820-1.000"), Eye Dimension 1 11/16"

Series Number : 130096

Status : Active

Product Category : Cable Grips

Engineering Number : 36554



Documents & Resources

Drawings

[1300960063_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Cable Grips
Series	130096
Description	Safeway Wire Mesh Grip, Straight Male, Cable Diameter 20.83-25.40mm (.820-1.000"), Eye Dimension 1 11/16"
Product Name	Safeway
Type	Strain Relief Grip
UPC	78678836554

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	20.83-25.40mm (.820-1.000")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	N/A
Net Weight	24.040/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A