Part Number : 1301460016
Product Description : Watertite Extreme Cordset 16 Gauge SOOW, 3 Pole/3 Wire, Cordset Length 7.62m (25.0'), Non-NEMA 15A/125V, 10A/250V
Series Number : 130146
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 14W07A163



Documents and Resources

Drawings

1301460016_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Cordset 16 Gauge SOOW, 3 Pole/3 Wire, Cordset Length 7.62m (25.0'), Non-NEMA 15A/125V, 10A/250V
IP Rating	IP69K
NEMA Configuration	Non-NEMA
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678898069

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	16/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Lighted Connector	No

Downloaded from Arrow.com.

Locking Blade	No
Net Weight	0.752/kg
Poles	3-pole/3-wire
Receptacle Type	Single

Downloaded from Arrow.com.