
1241768-1 Product Details



Active

View 3D PDF

Micro-Power & Power Quadlok System

MPQ/MQS ST-STE40+2P

1241768-1

TE Internal Number: 1241768-1

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Product Highlights View All

- Applies To Printed Circuit Board
- Connector
- Connector Assembly
- Connector Style = Header
- 40 Positions

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Type	Connector
Connector Type	Connector Assembly
Sealed	No

Termination Features

Termination Method to PC Board	Through Hole - Solder

Body Features

Material	PA 66

Contact Features

Contact Type	Tab
Contact Style	MQS
Tab Contacts	Without
Tab Contact Size	2.8
Number of MQS Contacts	24
2.5mm Pin Diameter Contacts	Without
Number of Power Contacts	16
Contact Finish	Tin

Housing Features

Connector Style	Header
Centerline, Matrix (mm [in])	2.54 x 2.54 [.100 x .100]
Header Color	Black

Configuration Features

Number of Positions	40
Fiber Optic Contacts	Without
Number of 2.8 Tab Contacts	16
Staggered Centerline	Without

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 240°C
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Applies To	Printed Circuit Board
Mates with Centerline	2.54 x 2.54 [.100 x .100]

Other

Brand	AMP

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback

[+] Feedback

Downloaded from Arrow.com.