



Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Colour	Black Grey
Depth	30.5 cm
Height	15.2 cm
Net weight	9.55 kg
Width	26.7 cm

Input

Network frequency	50 Hz
Max line current	63 A
Input voltage	400 V 3 phases

Output

Max current draw	63 A
Number of power socket outlets	1 IEC 60309
Output voltage	230 V 400 V 3 phases

Conformance

Product certifications	CE VDE
------------------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	0...30 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...4572.00 m

Packing Units

Package 1 Weight	11.36 kg
Package 1 Height	17.8 cm
Package 1 width	45.7 cm
Package 1 Length	43.2 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------