



Part Number : [1301080162](#)
Product Description : Super-Safeway Twin Tube
64W Fluorescent Work Light with 16/3 SJOW 7.62m
(25.0') Cord Length
Series Number : 130108
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1350



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108
Description	Super-Safeway Twin Tube 64W Fluorescent Work Light with 16/3 SJOW 7.62m (25.0') Cord Length
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678867148

Agency

UL	E174254
----	---------

Electrical

Lamp Wattage - Maximum	64W
Lumens	5700
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJOW
Depth	190.75mm (7.510")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	82.55mm (3.250")
Lamp Type	F32/T8
Length	1.39m (54.620")
Material - Globe	Butyrate

Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Adjustable Brackets
Outlet	None
Packaging Type	Carton

This document was generated on Sep 16, 2025