Part Number : 1210503392
Product Description : mPm DIN Valve Connector, Form B - 11mm, 2 Pole Plus Ground, PUR ULCable Pigtail, Yellow LED, Black Nitrile Gasket, 115V
Series Number : 121050
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E462B2A50021S0L



Documents and Resources

Drawings

1210503392_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 7(a); 7(c)-I per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	121050
Description	mPm DIN Valve Connector, Form B - 11mm, 2 Pole Plus Ground, PUR ULCable Pigtail, Yellow LED, Black Nitrile Gasket, 115V
IP Rating	IP65
Product Name	mPm
Protocol	N/A
Type	Single Ended
UPC	78172534604

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	115V

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN B - 11mm
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	PUR UL
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A

Downloaded from Arrow.com.

Material - Plating Mating	Gold
Net Weight	185.000/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	20

Downloaded from Arrow.com.