



Part Number : [5046182012](#)
Product Description : SlimStack Board-to-Board
Receptacle, 0.35mm Pitch, SSB6 Standard Series,
0.60mm Mated Height, 2.00mm Mated Width, 20
Circuits
Series Number : 504618
Status : Not Recommended For New Design
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

[5046182012 sd.pdf](#)

Specifications

[5046180000-A00.pdf](#)

[5046180000-000.pdf](#)

[PS-504622-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Board-to-Board Connectors
Series	0.35, SSB6
Description	SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB6 Standard Series, 0.60mm Mated Height, 2.00mm Mated Width, 20 Circuits
Application	Board-to-Board
Component Type	PCB Receptacle, Receptacle
Product Name	SlimStack
UPC	191128130325

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V

Physical

Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.60mm
Mated Width	2.00mm

Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	12.282/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.35mm Pitch SlimStack Board-to-Board Plugs	<u>504622</u>

This document was generated on Apr 12, 2026