



Part Number : [1301050032](#)
Product Description : Watertite Wet Location 30W
12V Spotlight with Screw Release Guard, Battery Clips
16/2 SOOW, Overall Length 15.24m (50.0')
Series Number : 130105
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1606



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130105
Description	Watertite Wet Location 30W 12V Spotlight with Screw Release Guard, Battery Clips 16/2 SOOW, Overall Length 15.24m (50.0')
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678862534

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	30W
Lumens	300
On/Off Switch	No
Voltage (Fixture) - Maximum	12V

Physical

Bulb Type	Quartz Halogen
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Secondary	16/2 SOOW
Depth	N/A
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	127.00mm (5.000")
Lamp Type	PAR36

Length	228.60mm (9.000")
Material - Guard	#10 Gauge Vinyl Coated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 10, 2025