

(Search)



Check Stock

[Products](#)

[Applications](#)

[Resources](#)

[About Us](#)

[Where to Buy](#)

[News & Events](#)

[Contact Us](#)

[Login](#)

Part Number : 5530222300F



5530222300F



[Share](#) | [Facebook](#) | [Twitter](#) | [LinkedIn](#)

General Description

Series	553
Configuration	3 mm Lens
Description	3 mm Bi-Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25°)

Reverse Current	10 @ Vr = 5V
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

LED Type	Low Current
Color	Green
Peak Wave Length	565
LED Position	1,2
Luminous Intensity Min	1
Luminous Intensity Typical	1.6
Forward Voltage Typical	1.9
Forward Voltage Max	2.2
Test Current mA	20mA
Power Dissipation Max	20mW