



Introducing

Left and Right Hand Plugs
3.5 mm and 3.81 mm Pitch

Left and Right hand plugs allow additional configurations of wire access angles to be applied to standard 3.5 mm & 3.81 mm vertical and right angle headers. These rising, screw clamp plugs mate to industry standard open and closed end headers on the same centerline spacing.

TE connectivity

Downloaded from Arrow.com.



KEY FEATURES

- Multiple wire access angles (90° & 270°) to header interface
- Mates with industry standard headers on the same centerline spacing
- Available in multiple colors
- Custom marking and printing is available
- Plugs are end to end stackable without loss of centerline spacing

APPLICATIONS

Wire-to-board applications requiring field wiring termination

Industrial Controls : control and power wiring

HVAC Controls : control and power wiring

ELECTRICAL

- 11 amps
- 300 volts

MECHANICAL

- 14–30 AWG
- -40°C to + 110°C

STANDARDS AND SPECIFICATIONS

Application Spec : 114-20079

MATERIALS

UL 94-VO

Housings : Made from PA 6.6

Clamps : Nickel plated brass

Contacts : Tin plated phosphor bronze

Downloaded from Arrow.com.

PRODUCT OFFERING

3.5 mm Right Hand Plug	
PN	Position
1986370-2	2
1986370-3	3
1986370-4	4
1986370-5	5
1986370-6	6
1986370-7	7
1986370-8	8
1986370-9	9
1-1986370-0	10
1-1986370-1	11
1-1986370-2	12
1-1986370-3	13
1-1986370-4	14
1-1986370-5	15
1-1986370-6	16


3.5 mm Left Hand Plug	
PN	Position
1986371-2	2
1986371-3	3
1986371-4	4
1986371-5	5
1986371-6	6
1986371-7	7
1986371-8	8
1986371-9	9
1-1986371-0	10
1-1986371-1	11
1-1986371-2	12
1-1986371-3	13
1-1986371-4	14
1-1986371-5	15
1-1986371-6	16

3.81 mm Right Hand Plug	
PN	Position
1986374-2	2
1986374-3	3
1986374-4	4
1986374-5	5
1986374-6	6
1986374-7	7
1986374-8	8
1986374-9	9
1-1986374-0	10
1-1986374-1	11
1-1986374-2	12
1-1986374-3	13
1-1986374-4	14
1-1986374-5	15
1-1986374-6	16


3.81 mm Left Hand Plug	
PN	Position
1986375-2	2
1986375-3	3
1986375-4	4
1986375-5	5
1986375-6	6
1986375-7	7
1986375-8	8
1986375-9	9
1-1986375-0	10
1-1986375-1	11
1-1986375-2	12
1-1986375-3	13
1-1986375-4	14
1-1986375-5	15
1-1986375-6	16

PRODUCT DIMENSIONS

Left Hand Version



Right Hand Version



Downloaded from Arrow.com.

FOR MORE INFORMATION

te.com/products/terminalblocks

TE Technical Support Center

Internet:	te.com/help
USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.
*as defined www.te.com/leadfree

te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved.

3-1773455-5 CIS WR 08/2011

TE Connectivity and the TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

Downloaded from Arrow.com.