



HIRSCHMANN

A BELDEN BRAND

Product information BAT-ANT-N-6ABG-IP65

Industrial Ethernet:Industrial Wireless LAN:Wireless Accessories :Wireless LAN Antennas:BAT-ANT-N-6ABG-IP65

<https://catalog.beldensolutions.com:443/link/57078-24455-49859-24498-24499-64580/en/conf/ui/state>

Name BAT-ANT-N-6ABG-IP65



Hemispherical antenna for 2.4 and 5 GHz band

Delivery informations

Availability available

Product description

Description Hemispherical antenna for 2.4 and 5 GHz band

Type BAT-ANT-N-6ABG-IP65

Order No. 943 981-004

Cable length 1 m

Cable specification N-plug to N-plug

Radio technology

Range refer to antenna distance calculator

Frequency band 2400 MHz - 6000 MHz

Polarisation linear, vertical

Elevation, Azimuth vertical hemispherical, horizontal 360°

VSWR 2

Gain 2.4 GHz: 6.0 dBi; 5 GHz: 8.0 dBi with 1sqm ground plate

Antenna connector N female

Ambient conditions

Operating temperature -40 °C to +80 °C

Storage/transport temperature -40 °C to +80 °C

Wind load 10 N at 160 km/h

Mechanical construction

Dimensions (W x H x D) Ø 86 mm x 43 mm

Mounting ceiling, cabinet

Protection class IP65, with sealing ring

Material ASA

Weight 0.3 kg

Scope of delivery and accessories

Scope of delivery antenna, 1 m cable, pigtail, sealing ring

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com



HIRSCHMANN

A **BELDEN** BRAND

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.