Part Number : 1300080112
Product Description : Mini-Change C-Size Single-Ended Cordset, 10 Poles, Female (90°) to Pigtail, 22 AWG, PVC Cable,10.0m (32.81') Length
Series Number : 130008
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 301001A04M100



Documents and Resources

Drawings

1300080112_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 10 Poles, Female (90°) to Pigtail, 22 AWG, PVC Cable,10.0m (32.81') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Single Ended
UPC	78678842226

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	600V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC

Downloaded from Arrow.com.

Material - Connector Body	PVC
Material - Contact	Brass
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	1367.630/g
Orientation	90° to Pigtail
Poles	10
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	N/A
Wire Size (AWG)	22

Downloaded from Arrow.com.