Part Number : 1301430113
Product Description : Super-Safeway Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-15, 125V
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 1447D163



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Super-Safeway Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-15, 125V
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Specialty	N/A
Type	Cordset
UPC	78678879552

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	16/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	30.48m (100.0')
Lighted Connector	No
Locking Blade	No
Net Weight	2238.297/g

Downloaded from Arrow.com.

Poles	2-pole/3-wire
Receptacle Type	Single

Downloaded from Arrow.com.