

# 00511700 & 00519700 CONNECTORS

7-Pole Plastic Body Plugs • 12V • ISO 1724 • ISO 3732

00519700  
00519200

00519000  
00519100



00511700

00511900

## Description

The series consists of a N (Normal) version complying to ISO 1724, which is generally used for standard applications, and a S (Supplementary) version complying to ISO 3732 to be used for additional connections. The latter can easily be recognized by its WHITE colouring and by the different order of the contacts, thus preventing an incorrect connection to the N version. Littelfuse supplies these connectors in plastic body with screw and flat contacts.

Included in the range of plugs are also the following special version clip-plug: 00511700 - 00511900 - 00512700.

## Features and Benefits

- Standards: Conforms to ISO 1724 & ISO 3732 recommendations and standards.
- Accepts all 7-pole sockets that conform to ISO 1724 & ISO 3732.
- The screw contacts version is mainly intended for the replacement market (aftermarket)
- The flat terminals version is generally preferred by harness manufacturers.


## Specifications Overview

<b>Voltage:</b>	12V
<b>Standards:</b>	ISO 1724 ISO 3732

## Web Resources

Download 2D print and technical resources at:  
[littelfuse.com/connectors](http://littelfuse.com/connectors)

## Ordering Information

PART NUMBER			ISO	PIN MATERIAL	TERMINAL TYPE
BULK 20 pcs.	BULK 100 pcs.	BULK 100 pcs. 			
00519700	00519790	00519799	1724	Brass	screw
00519780			1724	Nickel plated brass	screw
00511700	00511790	00511799	1724	Brass	screw
00511780	00511785		1724	Nickel plated brass	screw
00519200			1724	Brass	flat
00519280			1724	Nickel plated brass	flat
00519000			3732	Brass	screw
00519100			3732	Brass	flat
00512700	00512790	00512799	1724	Brass	flat
		00512795	1724	Nickel plated brass	flat
00511900	00511990	00511999	3732	Brass	screw

## Accessories

PART NUMBER	IMG.	PLUG	DESCRIPTION OF ACCESSORIES
00600200 (20 pcs)	1		Rear protection cap for 7 pin 12V to all plugs
00606900 (10 pcs)	1	00511700 00511900 00512700	Rubber grommet with 2 cable outlets for clip-plugs

1



2

