

T 3262 300 U

Description	Male panel connector 3 pole IP40; solder; silver; screw locking
IP-class mated	IP40
number of positions (w/o PE)	3
rated current (40 °C)	5 (A)
rated voltage	300 (V)


add to cart

add to favorite

send request







Technical data | Downloads

General Characteristics		
contact diameter		1,5 mm
gender		male
IP-class mated		IP40
locking system		screw coupling
number of positions (w/o PE)		3
part category		male receptacle
termination		solder pin
Further Characteristics		
max. wire gauge		0.5
min. wire gauge		0.09
RoHS Compliant Yes		X
Electrical Characteristics		
rated current (40 °C)	(A)	5
rated voltage	(V)	300

Downloaded from Arrow.com.

Read more

catalogues and additional information.
Read more

electronic and fiber optic connectors worldwide. Read more

Downloaded from Arrow.com.