








P.C.B Layout

MATERIAL:
HOUSING:PBT+30%G.F UL 94V-0
CONTACT:BRASS T=0.25mm
SHELL:SPCC T=0.30mm
PLATING:
CONTACT: GOLD AND TIN OVER NICKEL PLATING
SHELL: NICKEL OVER ALL PLATING
SPECIFICATION:
CURRENT-MAX[AMPS]1.5A
VOLTAGE-MAX[VOLTS]:30V
WITHSTANDING VOLTAGE:500V AC
CONTACT RESISTANCE[OHMS]:30mΩ MIN
INSULATION RESISTANCE[OHMS]:1000MΩ MIN
INSULATION COLOR:WHITE
ENVIRONMENTAL:
TEMPERATURE RANGE:-40°C TO+105°C

09/14-15	yang		NEW DWG		AO
DATE	DR.BY	ECN.NO.	DESCRIPTION		MARK VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表		CnC Tech, LLC			
			TITLE: USB 4P AM SMT 貼片式成品		
X.X	±0.38	X.X° ±3.00°	APPD:	PRODUCT NO: 1001-011-01101	
X.XX	±0.25	X.XX° ±2.00°	CHECK:	DATE	SCALE UNIT TYPE PAGE
X.XXX	±0.10	X.XXX° ±1.00°	DRAW:	2015.09.09	1:1 mm Z 1 / 1