



C2G
Discontinued - D-Link® DEM-311GT Compatible 1000Base-SX SFP (mini-GBIC) Transceiver Module (Multimode, 850nm, 550m, LC)
Part No. DEM-311GT-LEG



This D-Link® DEM-311GT compatible SFP transceiver provides 1000Base-SX throughput up to 550m over multi-mode fiber (MMF) at a wavelength of 850nm using a LC connector. It is guaranteed to be 100% compatible with the equivalent D-Link® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of D-Link®, as well as to comply with MSA (Multi-Source Agreement) standards to ensure seamless network integration. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits	
Supports data rates up to 1000Mbps	SFP transceiver module
LC ports designed for use with Multimode Fiber	850nm wavelength signaling
Supports up to 550 meters of cabling	

Specifications			
General Info			
Product Line	C2G	Color	Silver
UPC Number	757120669197	Country Of Origin	United States
Application Sector	Commercial, Industrial	Type	Transceiver
Technical Information			
Fiber Optic Cable Type	Multimode	Max Distance Support	550 m
Connector 1	SFP+ Male		