


[English](#)
[日本語](#)
Electronics

a vital part of your world

Find
Answers:

Tuesday, 18 October, 2005

CATALOG

 Cross Reference

[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

-  [Part Number Search](#)
-  [Document Search](#)
-  [Product Type Search](#)
-  [Product Family Search](#)
-  [Alphabetical Search](#)
-  [RoHS/ELV Compliance & Alternates](#)
-  [CAD Model Search](#)
-  [Brand Search](#)
-  [Tool Search](#)
-  [Multiple Part Comparison](#)
-  [Lead Free Solutions](#)
-  [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
click here

Terminals and Splices

 Ring and Spade Tongue Terminals

AMP

60319-2



Active

**Directive 2002/95/EC
Compliant**

RoHS Compliant

(Corporate P/N: 60319-2)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
✦ General Info ✦ Sales Info ✦ Assembly Subcontractors	✦ Pricing ✦ Product Availability	✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
Government/Industry Qualification:	No
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Terminal Shape:	Ring Tongue
Receptacle Style:	Straight
Body Style:	AMPLIVAR
Barrel Type:	Open Barrel
Wire/Cable Type:	Magnet Wire

Other Properties:

Stock Thickness (mm [in]):	0.51 [0.020]
----------------------------	--------------

Wire Range (mm [AWG]):	0.574-0.912 [23-19]
Insulation:	No
Insulation Support:	Insulation Support
Insulation Diameter (mm [in]):	2.54-3.56 [.100-.140]
Stud Size:	10
Stud Diameter (mm [in]):	5.00 [0.197]
Shape:	RING-028
Heavy Duty:	No
Packaging Method:	Strip
Material:	Brass
Finish:	Tin

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]