



Alle Rechte vorbehalten/ *All rights reserved*









Note: Jack-screws are not pre-mounted to allow mounting from any ends

SPECIFICATIONS

Filter type	C
Capacitance	470 pF±20%
Working voltage	100 V
Current rating	6,5 A

Minimum insertion loss

FREQUENCY (MHz)	ATTENUATION (dB)
5	-
10	1
50	10
100	15
500	35
1000	32

Mod.	Dat.	Name
34901	01/04/08	BB
34894	12/03/08	PK
	03/09/07	JS

	Dat.	Name
Detail.	03/09/07	JS
Insp.		
Stand.		

All Dim. in mm
Orig. Size DIN A 4

HARTING EURL
F-95972 Paris

Male / Female D-Sub filter adapter, 9 poles, 470 pF

Maßstab/ *Scale* 1,5:1

TB 09 64 100 7220

Sub.

Blatt/ *Page* 1/1

Downloaded from Arrow.com.