



Part Number : [1062831005](#)
Product Description : Quad Small Form-factor Pluggable (QSFP) Optical Jumper Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP Multimode 50/125µm 3.00mm Round Cable Plenum, High Bandwidth (OM3), 5.0m (16.40') Length, Aqua Cable
Series Number : 86004
Status : Active
Product Category : Fiber Optic Cable Assemblies

Documents and Resources

Drawings
[1062831005 sd.pdf](#)
Specifications
[1062840501-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dioctyltin dilaurate, stannane, dioctyl-, bis(coco acyloxy) derivs., and any other stannane, dioctyl-, bis(fatty acyloxy) derivs. wherein C12 is the predominant carbon number of the fatty acyloxy moiety per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86004
Description	Quad Small Form-factor Pluggable (QSFP) Optical Jumper Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP Multimode 50/125µm 3.00mm Round Cable Plenum, High Bandwidth (OM3), 5.0m (16.40') Length, Aqua Cable
Connector to Connector	MTP-to-MTP
Mode	Multimode Enhanced
Product Name	MTP,QSFP Plus,QSFP+
UPC	822350973984

Agency

CSA	LR64395
UL	E72548

Physical

Boot Type	Straight
Cable Length	5.0m

Cable Size	3.00mm
Fiber (Core/Cladding)	50/125μm
Net Weight	52.000/g
Single Ended	No
Wire/Cable Type	OM3 Plenum

This document was generated on May 27, 2026