

© – TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	PCN-25-266602	08AUG2026	GSK	CAS

1. CONTACT BODY: 30 µIN MIN GOLD IN CONTACT AREA, 5 µIN MIN GOLD ON REMAINDER, OVER 30 µIN MIN NICKEL.
   CONTACT POST: 100 µIN MIN TIN OVER 50 µIN MIN NICKEL.
2. CONTACT BODY: 30 µIN MIN GOLD IN CONTACT AREA, OVER 30 µIN MIN NICKEL.
   CONTACT POST: 100 µIN MIN TIN–LEADED, OVER 50 µIN MIN NICKEL.






OBSOLETE	.220	1986377-3
	.557	1986377-2
	.220	1986377-1
	DIM A	PART NUMBER



POST ARRANGEMENT ON REAR FACE
SCALE 6:1



1986377-2

YES	1	1986377-3
YES	2	1986377-2
NO	1	1986377-1
4-40 THREADED INSERTS	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13 [.005]
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL: SEE CALLOUTS
FINISH: –

DWN S SCHLEGEL 2/27/08
CHK S HEADER 2/27/08
APVD S HEADER 2/27/08
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT

TE Connectivity

NAME: RECEPTACLE ASSY, POSTED, REV SEX, SERIES 1, SIZE 13-7, CPC

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1986377	—

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV E

1986377

Downloaded from Arrow.com.