



Part Number : [1062250010](#)
Product Description : MPO Female-to-MPO Female Trunk Cable Assembly, 9/125µm, 4.80mm, Singlemode, 12 Fiber, Plenum, OS2, 25.0m Length, Yellow
Series Number : 106225
Status : Active
Product Category : Fiber Optic Cable Assemblies




Documents & Resources

Drawings
[Drawing 1062250010_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106225
Description	MPO Female-to-MPO Female Trunk Cable Assembly, 9/125μm, 4.80mm, Singlemode, 12 Fiber, Plenum, OS2, 25.0m Length, Yellow
Connector to Connector	MPO-to-MPO
Mode	Singlemode
Product Name	MPO
UPC	191128250221

Physical

Boot Type	Straight
Cable Length	25.0m
Cable Size	4.80mm
Fiber (Core/Cladding)	9/125μm
Net Weight	551.853/g
Single Ended	No
Wire/Cable Type	12 Fiber OS2 Plenum

This document was generated on Sep 03, 2023
