

Product Line

DeepTronica

>

Single Pair Ethernet

>

ZConnect

>

Ceres

>

X-Lok

>

M Series

>

FLOS & FLOS+

>

Power

>

RBL

>

HS-Lok

>

NMEA 2000

>

Mini

Micro

Accessory

Heavy Duty Shielded

>

RJ

>

USB

>

SSL

>

HDMI

>

DVI

>

Fiber Optic

>

RF

>

Cable Joiner

>

Cable Gland

>

Pressure Relief Vent

>

LED Light Guide

>

D-Sub

>



HMC-050505-FMF-TS001

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A

Shielded: Metal, Non-shielded

Jacket Material: PVC

Certificate: NMEA 2000

You must login first for view the price

Quantity

-

1

+

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

M Series....
CAP-WBDMSMA2
-40°C ~ +105°C

- 0 +

☐

NMEA 2000, Micro..
HMC-000505-...
-20°C ~ +80°C

- 0 +

☐

NMEA 2000, Micro..
HMC-000505-...
-20°C ~ +80°C

- 0 +

☐

NMEA 2000, Micro..
HMC-000505-...
-20°C ~ +80°C

- 0 +

☐

NMEA 2000, Micro..
HMC-000505-...
-20°C ~ +80°C

- 0 +

☐

NMEA 2000, Micro..
HMC-000505-...
-20°C ~ +80°C

- 0 +

☐

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type T Adaptor
Shielded Metal, Non-shielded	No. of Contacts 05
Connector Gender Female	Backshell N/A
Mating Style Screw Thread	IP Rating IP68
Assembly Style N/A	
More Options	

People Also Bought

HMC-050505-FMF-...

CC-02AFMM-QR8E10

M12B-04BFFM-...

AB-AZ17ML-AZML-...

CD-04AMFM-RL8010

[ABOUT AMPHENOL LTW](#)

[SUPPORT](#)

[PARTNERS](#)

[DOWNLOAD CENTER](#)

[FEEDBACK](#)

Downloaded from [Arrow.com](#)