



+ SHIPS FREE
UPS FLAT RATE
MILITARY
DISCOUNT
IBEW-NECA
DISCOUNT



Contact Us

Account | Wishlist | Quick Order | Log In

100% Lifetime Guarantee

[Home](#) → [Tool Types](#) → [Screwdrivers](#) → [Precision Torx® Screwdrivers](#)

Precision Torx® Screwdrivers



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Torx Size	OAL MM	Blade Length Inch	Price	Qty
26701	Precision Torx® Screwdriver T1 x 40mm	T1	120	1.6		<input type="button" value="0"/>
26702	Precision Torx® Screwdriver T2 x 40mm	T2	120	1.6		<input type="button" value="0"/>
26703	Precision Torx® Screwdriver T3 x 40mm	T3	120	1.6		<input type="button" value="0"/>
26704	Precision Torx® Screwdriver T4 x 40mm	T4	120	1.6		<input type="button" value="0"/>
26705	Precision Torx® Screwdriver T5 x 40mm	T5	120	1.6		<input type="button" value="0"/>
26706	Precision Torx® Screwdriver T6 x 40mm	T6	120	1.6		<input type="button" value="0"/>
26707	Precision Torx® Screwdriver T7 x 40mm	T7	120	1.6		<input type="button" value="0"/>
26708	Precision Torx® Screwdriver T8 x 40mm	T8	120	1.6		<input type="button" value="0"/>

SKU	Product	Torx Size	OAL MM	Blade Length Inch	Price	Qty
26709	Precision Torx® Screwdriver T9 x 50mm	T9	145	2		<input type="button" value="0"/> 
26710	Precision Torx® Screwdriver T10 x 50mm	T10	145	2		<input type="button" value="0"/> 
26715	Precision Torx® Screwdriver T15 x 60mm	T15	170	2.4		<input type="button" value="0"/> 
26720	Precision Torx® Screwdriver T20 x 60mm	T20	170	2.4		<input type="button" value="0"/> 

[Add to Cart](#)



We accept 

Frequently bought together



Price for all selected : [Add selected to cart](#)

This item: Precision Torx® Screwdrivers

Pocket Clip For Precision Screwdrivers

Green Canvas Pouch for Sets

Details

Wiha special chrome-vanadium-molybdenum tool steel
 Through hardened for best wear resistance
 Corrosion protective Vapor Chrome Finish
 Exact fit precision CNC machined tips
 Precision handle is made of high quality cadmium free plastic
 Molded on handle for permanent bond to blade
 The tapered faceted shape allows rapid rotation
 Handles are proportioned to blade size for optimum torque
 Finger tip rotation cap for precise turning and control
 Professional Quality Made In Germany

Additional Info

Head Type	 torx
Country of Manufacture	Germany
Handle Grip Types	Precision

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)





Precision Torx® Screwdriver 6
Piece Set T6-T15

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH Schonach Germany](#)

Monday - Friday Office Hours 7am - 5pm CST USA

1348 Dundas Cir,
Monticello, MN 55362

Customer Service Email:

cservice@wihatools.com

Tel: [763-295-6591](tel:763-295-6591)

Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

Over 5000 Professional Quality Wiha Tools In Stock



Newsletter

[Subscribe](#)

© 2017 Wiha Tools USA. All Rights Reserved.

SHIPS FREE

