

Search within category

GO

BUY NOW

DESIGN / INSTALL



STP28X18MOR

Category 6A Performance, 28AWG, F/UTP Patch Cord, CM/LSZH, Orange, 18m.

- Specs
- Packaging Details
- Documents

★ Add to Favorites

Add to BOM

|                          |                                |
|--------------------------|--------------------------------|
| Product Type             | Copper Patch Cord              |
| Performance Level        | Category 6A/Class EA           |
| Cable Color              | Orange                         |
| Length (ft.)             | 59.06                          |
| Length (m)               | 18                             |
| Flammability Rating      | CM/LSZH                        |
| Termination End 1        | Modular Plug                   |
| Termination End 2        | Modular Plug                   |
| Standards                | PoE,PoE+                       |
| Wiring Scheme            | T568B                          |
| CE Compliant             | Yes                            |
| Nominal Cable O.D. (In.) | 0.185                          |
| Nominal Cable O.D. (mm)  | 4.7                            |
| Operating Temperature    | 14°F to 140°F (-10°C to 60°C)  |
| Storage Temperature      | -40°F to 158°F (-40°C to 70°C) |
| UL5A Listed              | -                              |
| Cable Type               | F/UTP                          |
| Product Group Assignment | Copper                         |
| UNSPSC                   | 43223303                       |
| RoHS Compliancy Status   | Compliant                      |
| Min. Order Qty.          | 1.0000                         |