MVG 12/25



Product code: 64000250

MASTERVOLT
THE POWER TO BE INDEPENDENT

Downloaded from Arrow.com.

In Gel batteries, the electrolyte is absorbed by a Gel. This type of battery is entirely maintenance-free and has no gas formation with normal use. As no extra ventilation is required, Gel batteries can be installed anywhere. They are ideal as service battery and for cyclical use, and can be charged very quickly.

- Perfect service battery for medium sized and large 12 V and 24 V systems.
- Extremely long lifespan.
- No gas formation with normal use.
- Fast recharge, high charge current possible.
- For intensive cycle use with a high number of charge/discharge cycles.
- Very low self-discharge.
- High return on investment.
- Two year warranty.

Downloaded from Arrow.com.

Specifications

General specifications

Nominal battery voltage	12 V
Nominal battery capacity C20	25 Ah
Max. charge current	12.5 A
Terminals	A-type
Max. outer dimensions (incl. terminals/grip handles), lxwxh	167 x 176 x 126 mm 6.6 x 6.9 x 5.0 inch
Weight	9.6 kg 21.2 lb

Technical specifications

CCA to DIN	110 A
CCA to SAE	175 A

MASTERVOLT
THE POWER TO BE INDEPENDENT

Downloaded from Arrow.com.