




WIRING TABLE


C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
67	AWG 30	67
68	AWG 30	68

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT(500VDC)TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE & LOT INFORMATION
HARTING P/N & REVISION

HARTING P/N	Cable length(L)
3315 243 010 0122	100 ± 3
3315 243 020 0122	200 ± 5
3315 243 050 0122	500 ± 10

		All Dimensions in mm Original Size DIN A3		Scale 1.5:1	Free size tol. \\	Ref. \			
				Sub. \					
	All rights reserved			Created by ZHENGL	Inspected by WANGE	Standardisation CHENJU	Date 2018-10-12	State Final Release	
	Department HCS - CN			Title Har-Flex 68Pole,Dul-end,With SR,L=XXMM		Doc-Key / ECM-Nr. 100586962/UGD/000/A 500000141225			
HARTING Customised Solutions D-32339 Espelkamp				Type TB	Number 33150023			Rev. A	Page 1/1