

Cable tie tool for 2.5 - 4.8mm, manual, 0.279kg, blue

Art.-No. 110-77002 | EVO7iSP-MET/PL-BU | [Details](#)



- Ergonomic, slip-proof handle for a comfortable and secure grip
- Extremely low-maintenance
- Fast and precise application with minimum effort (TLC mechanism)
- Convenient and simple tension adjustment
- Extended, slim nose for use in narrow spaces
- Housing made of resilient and lightweight glass fibre-reinforced polyester
-



More products in this product group:

[Manual tensioning tool plastic housing >](#)

Application	HellermannTyton's EVO 7i industrial-grade, mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 7i's Tension/Lock/Cut technology delivers performance, safety and comfort for operators. Calibrated tensioning assures consistent wire bundle tension before flush cut-off. Available in a standard grip span (EVO 7i) or short grip span (EVO 7iSP) for smaller hands. Additional accessories are available.
Colour	Blue (BU)
Description	EVO7iSP
For Cable Tie Width	0.10 - 0.19 "
For Cable Tie Width	2.5 - 4.8 mm
For Ties	T18, T30, T40, T50, T80, IT18, IT50
Material	Metal (MET), Plastic (PL)
Operation	manual
PART DESCRIPTION	EVO7iSP-MET/PL-BU
Pack Cont.	1 pc.
Package Content packed in	box
Product Family	EVO7iSP up to 4.8 mm strap width
Product Group	Manual tensioning tool plastic housing
Strap Thickness max.	1.5 mm
Tool property	Manual clipping
Tool suitable cable tie material	Plastic
Type	EVO7iSP

Product Dimensions

Length (L)	192 mm
Strap Width max.	4.8 mm
Tension Setting	Adjustable
Weight/Unit	0.279 kg
Width (W)	33 mm

CE Certification	NO
CSA Certified	No
ELV compliant (Article 4 - 2)	YES
Hazardous Goods	No
ROHS compliant	Yes
Specifications	
UL Listed (US and Canada)	No
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No
UL Recognized (US and Canada)	No

Logistics and Packaging

Country of Origin	CN
Customs Number	82055980
GTIN-13 / EAN	4031026621784
Packaging 1 - Height (m)	0.055 m
Packaging 1 - Length (m)	0.235 m
Packaging 1 - Qty	1
Packaging 1 - Type	carton
Packaging 1 - Volume (m³)	0.00239 m³
Packaging 1 - Weight (kg)	0.779 kg
Packaging 1 - Width (m)	0.185 m

More Information

ETIM 7.0 Key	EC000453
ETIM 8.0 Key	EC000453
ETIM 9.0 Key	EC000453
UNSPSC Key	27112410

