



LAYOUT DIMENSIONS (after plating)
CONNECTOR SIDE VIEW



NOTE:
insulator material:thermoset

LEAD FREE PART NUMBER

DB9W4S500G00LF
PART NUMBER

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8639-0003

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection	mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR 0.1° ±2°	LINEAR 0.X ±0.1 0.XX ±0.1 0.XXX ±0.1	size A3	Scale 1.5	
Dr	M PESSON	2008/01/16	0.X ±0.1	ECN	L508-0012	
Eng	PESSON	2008/01/16	0.XX ±0.1	Product family	D-SUB	Spec ref -
Chr	LEGARE	2008/01/16	0.XXX ±0.1			
Appr	LEGARE	2008/01/16				
FCI		SOCKET CONNECTOR		C-8639-2356		Rev. A
9W4 RIGHT ANGLE		catalog no		CUSTOMER sheet 1 of 1		