

CATALOG LISTING
4TP66-10
PAGE 1 OF 1
REPLACES
PR-6680
CHECK
REVISIONS
A CO 39765
SJS
2 FEB 78
B CO 44270
TMM
7 DEC 78
C CO 45979
SLB
30 APR 79
D CO47320
CEB
4 MAR 80
E CO 47824
GLW
6 MAY 80
F CO49167
JAP
16 JUL 81
G CO60064
SJS
19 AUG 85
H CO77697
TSM
15 JUN 94
J CO 79047
SAD
12 JAN 95
K CO-94417
CSL
24 NOV 99
FORMTEK
FO-82894
DRAWN
J A L 25 AUG 77
CHECK
GLH 25 AUG 77
CHECK
GLH 25 AUG 77

MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-TOGGLE FLUSH KEY

CATALOG LISTING
4TP66-10




THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CIRCUIT DIAGRAM

LUG SIDE

CENTER

OPPOSITE LUG



ELECTRICAL DATA


15A-125, 250 OR 277 VAC
1/2 HP-125VAC; 1HP-250, 277VAC
5A-125VAC "L" CODE L191

NOTES

1 - TERMINAL DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH

2 FURNISHED UNASSEMBLED

3 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.01)	±.030
TWO PLACE	(.001)	±.015
THREE PLACE	(.0001)	±.005
ANGLES		±

WEIGHT .22 LB EST