

Part Number : [1301040048](#)

Product Description : Haztex Incandescent
Hazardous and Wet Location Hand Lamp, 100W, 14/3
SOOW Cord Type, 30.48m (100.0') Cord Length

Series Number : 130104

Status : Active

Product Category : Lamps and Lights

Engineering Number : 61430D143



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130104
Description	Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W, 14/3 SOOW Cord Type, 30.48m (100.0') Cord Length
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678861435

Agency

CSA	LR39801
UL	E30252

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	30.48m (100.0')
Cord Length - Secondary	N/A
Cord Type - Primary	14/3 SOOW
Depth	127.00mm (5.000")

Duty	Hazardous, Wet Location
Guard Included	Yes
Guard Type	Cast Aluminum
Height	419.10mm (16.500")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 10, 2025