


Rev	AWO #	Description	Date	Appr
-		RELEASED	4/1/15	
A		UPDATE DRAWING	1/14/21	LH/LX

APPROVED: _____

DATE: _____ TITLE: _____







SPECIFICATIONS:
Material:
Insulator: PA66, rated UL 94V-0
Insulator color: Green
Screw: M2.0
Contact: Copper Alloy, Nickel Plated
Electrical:
Voltage rating: 300 V
Current rating: 8 A
Dielectric withstanding voltage: 1,600 VAC for 1 minute
Mechanical:
Wire Range: 16-28AWG
Torque: 0.2N-m
Wire strip length: 6-7mm
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

Positions: 02 thru 24
A= .150 [3.81] x No. of Spaces + .181 [4.60]
B= .150 [3.81] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	HR	4/1/15
CHECKED	KW	4/1/15
APPROVED		

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
EURO BLOCK, .150 [3.81] PITCH

SIZE	PART NO.	REV.
X	EB5A-XX-B	A

REF: S00067C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.