

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Label for ME ... F-UT ... TBUS ... housing, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 44 x 49 mm, Number of individual labels: 200

Your advantages

- The EML ... self-adhesive device markers are particularly well suited for marking various types of equipment in control, system, and control cabinet manufacturing
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML ... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EM ... markers in accordance with your requirements
- A wide range of marker sizes and colors are available for custom designs

Commercial Data

Item number	0828169
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	BG16
Product Key	BG2411
Catalog Page	Page 674 (C-1-2013)
GTIN	4046356484091
Weight per Piece (including packing)	138 g
Weight per Piece (excluding packing)	99.99 g
Customs tariff number	39269097
Country of origin	DE

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

Technical Data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	200
-----------------------------	-----

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white
Material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 5 °C
Recommended ambient temperature (storage/transport)	21 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	44 mm
Length	49 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 8.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

Accessories

THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/us/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/us/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/us/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/us/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/us/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

THERMOMARK-RIBBON 110 - Ink ribbon

5145384

<https://www.phoenixcontact.com/us/products/5145384>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMPLP... and PMM..., roll length: 300 m, width: 110 mm, color: black

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

THERMOMARK-RIBBON 110/50 - Ink ribbon

0800687

<https://www.phoenixcontact.com/us/products/0800687>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., roll length: 50 m, width: 110 mm, color: black

THERMOMARK-RIBBON 110 BU - Ink ribbon

0829544

<https://www.phoenixcontact.com/us/products/0829544>



Ink ribbon, roll length: 300 m, width: 110 mm, color: blue

EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

THERMOMARK-RIBBON 110 RD - Ink ribbon

0829543

<https://www.phoenixcontact.com/us/products/0829543>

Ink ribbon, roll length: 300 m, width: 110 mm, color: red



THERMOMARK-RIBBON 110 GN - Ink ribbon

0829542

<https://www.phoenixcontact.com/us/products/0829542>

Ink ribbon, roll length: 300 m, width: 110 mm, color: green



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com