

ENCLOSURE HARDWARE ▾

LED INDICATORS ▴

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDs

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES

PANEL MOUNT LED ASSEMBLIES

LED LIGHTING ▾

SOLUTIONS

RESOURCES ▾

FLPR2.5-SG



Flexible Light Pipe Assembly, 1mm. Fiber Optic Core, Right Angle, 4.2mm. Dia. Low Profile Lens, 2.5in. Length, 3mm LED, Super Green



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES

VALUE ADDED

CHECK STOCK

- Wavelength: 568nm, Typical Intensity: 50mcd, Color: Green
- Assembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED
- 4.2mm. Diameter Low Profile Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Front Panel Mount Lens



Enclosure Hardware
LED Indicators
LED Lighting

New Products
Locate a Distributor / Sales REP
Quality Assurance / RoHS

Product Info Center
Terms & Conditions
My Bivar



100%
Employee
Owned