

**MHHT-3-5K2-G-101**  
**MARINE HIGH VOLTAGE HEAT SHRINKABLE TERMINATION KIT**


**Components List:**

ITEM NUMBER	DESCRIPTION	QTY	U/M
1	Heat shrinkable tubing, 40"	6	PC
2	Heat shrinkable breakout Boot	1	PC
3	Sealant Mastic, red, 15" length.	6	PC
4	Stress Relieving Mastic (SRM), yellow, 24 " long	6	PC
5	SRM wedge for crotch, yellow	1	PC
6	Roll spring clamp	1	PC
7	Ground Braid, #4 AWG, 24" length	1	PC
8	Copper tape, 3/8" width, 8" length each	3	PC
9	Discharge control compound (grease) or DCC	2	PC
10	Copper mesh tape, 2" width	1	PC
11	Cable cleaning preparation kit	1	EA
12	Installation instructions (See note 2)	1	EA

**Notes:**

1. For use with 250 MCM or 400 MCM custom military marine cable: stranded, silicone insulated, flooded, with ground wires, an overall braided shield and low smoke cross-linked polyolefin jacketed.
2. Refer to TUS-41-3027 for installation instructions.

**CUSTOMER DRAWING**

		<b>Raychem Molded Parts</b> 300 Constitution Drive Menlo Park, CA 94025 USA		<b>Title</b> <b>MARINE HIGH VOLTAGE SHRINKABLE TERMINATION KIT</b>		
TYCO ELECTRONICS RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION				<b>Document No.</b> <b>MHHT-3-5K2-G-101</b>		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE SHOWN IN BRACKETS				<b>Rev.:</b> B		<b>Rev. Date:</b> March 16, 2010
<b>DRAWN BY:</b> UNGUYEN	<b>CAGE CODE:</b> 06090	<b>Org. Date:</b> 2/16/10	<b>File name:</b> ECO-10-005741	<b>SCALE:</b> None	<b>SIZE:</b> A	<b>SHEET:</b> 1 of 1

©2010 Tyco Electronics Corporation. All rights reserved.

If this document is printed it becomes uncontrolled. Check for the latest revision.