Part Number : 1212100045
Product Description : mPm DIN Valve Connector, Form C-8mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 230V, Amber LED, Transparent, Nitrile Gasket
Series Number : 121210
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : S25200TC4M0T



Documents and Resources

Drawings

1212100045_sd.pdf

Specifications

PK-121210-S25-001.pdf

PS-121201-001-001.pdf

STR-1251-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121210
Description	mPm DIN Valve Connector, Form C-8mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 230V, Amber LED, Transparent, Nitrile Gasket
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	884982538887

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	230V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	C - 8mm
Gender	N/A
Keyway	None

Downloaded from Arrow.com.

Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	9.789/g
Orientation	90° Angle
Pitch - Mating Interface	8.00mm
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire Size (AWG)	N/A

Downloaded from Arrow.com.