Upper part of housing - ME 22,5 OT-MSTBO KMGY FL 4AO - 1116376

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

DIN rail housing, Upper housing part for connectors with header, color: light gray (7035)

Key Commercial Data

Packing unit	1 pc
GTIN	4 063151 042745
GTIN	4063151042745
Weight per Piece (excluding packing)	16.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Item properties

Brief article description	Upper part of housing
Type	ME 22,5 OT-MSTBO KMGY FL 4AO
Order No.	1116376
Housing type	DIN rail housing
Type	Upper housing part for connectors with header
Mounting type	Latching with lower housing part

Material data

Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0
Housing material	Polyamide

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

PCB data

Mounting position	Vertical (horizontal DIN rail)
Type of PCB mount	Latching

Packaging information

Downloaded from Arrow.com.

Upper part of housing - ME 22,5 OT-MSTBO KMGY FL 4AO - 1116376

Technical data

Packaging information

Pieces per package	10
Denomination packing units	Pcs.

Standards and regulations

Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031

Phoenix Contact 2019 © - all rights reserved
http://www.phoenixcontact.com

Downloaded from Arrow.com.