

HONEYWELL  
PART NUMBER

78629

HONEYWELL PART NUMBER, PRESSURE  
SETTING AND DATE CODE

2X 1/4 BLADE TERMINAL

REV	DOCUMENT	CHANGED BY	CHECK
C	0068756	SBH 08SEP10	CMH

1/8-27 NPT

(2.4)

(Ø 1.47)

1. SINGLE CIRCUIT NORMALLY OPEN PRESSURE SWITCH.
2. CLOSING ADJUSTMENT RANGE .5 – 1 PSI.
3. SWITCH IS FURNISHED WITH STEEL BASE ASSY. (.500 HEX) AS A STANDARD UNLESS BRASS BASE ASSY. (.437 HEX) IS SPECIFIED AS AN OPTION BY CUSTOMER ADDING SUFFIX "B" TO THE HONEYWELL PART NUMBER ON THE PURCHASE ORDER, e.g. XXXXXB.
4. DIMENSIONS ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.

CUSTOMER: \_\_\_\_\_

APPROVED BY: \_\_\_\_\_

DATE: \_\_\_\_\_

CUSTOMER  
PART NO.: \_\_\_\_\_


CUSTOMER PRINT

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACES	X	±	—
ONE PLACE	.X	±	.020
TWO PLACE	.XX	±	.010
THREE PLACE	.XXX	±	.005
ANGLES	X	±	0° 30'

THIRD ANGLE PROJECTION



DRAWN

D MCGEE

24OCT01

CHECK

—

—

THIS DRAWING COVERS A PROPRIETARY ITEM  
AND IS THE PROPERTY OF HONEYWELL.  
THIS DRAWING IS NOT TO BE COPIED OR USED  
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994  
OTHER HONEYWELL ENGINEERING  
STANDARDS MAY APPLY

AUTOCAD

2D

**Honeywell**

TITLE

PRESSURE SWITCH N.O.  
BLADE TERMINALS  
5000 SERIES SWITCH

SIZE

A

TYPE

I

CAGE CODE

—

DRAWING NAME

78629

REV

C

SCALE

NONE

SHEET

1 OF 1