


Feed-through Type Receptacle Assemblies

Material & Finish :
Housing— Recognized by UL. Flame retardant grade, 94V-0 rated, 66 Nylon, (See chart for colors)
Contact— Phosphor bronze, pre-tin plated



* 3 ~ 13 pos. housing: single dimple (center)
** 14 ~ 20 pos. housing: double dimple





Section A-A

No. of Pos.	Dimensions B	C	D	E	Part Nos. of Receptacle Assemblies Wire Range AWG #28 (Green)	Wire Range AWG #26 (Natural)	Wire Range AWG #24 (Black)	Wire Range AWG #22 (Red)
3	2	5.0	7.8	10.0	—	—	172186-3	—
4	3	7.5	10.3	12.5	—	—	172186-4	—
6	5	12.5	15.3	17.5	172188-6	172187-6	172186-6	172185-6
8	7	17.5	20.3	22.5	172188-8	172187-8	172186-8	172185-8
10	9	22.5	25.3	27.5	1-172188-0	1-172187-0	1-172186-0	1-172185-0
14	13	32.5	35.3	37.5	1-172188-4	1-172187-4	1-172186-4	1-172185-4
16	15	37.5	40.3	42.5	1-172188-6	1-172187-6	1-172186-6	1-172185-6
20	19	47.5	50.3	52.5	2-172188-0	2-172187-0	2-172186-0	2-172185-0

Note : ( ) are shown for housing colors.

Downloaded from Arrow.com.