

956-3125 - 956 Heavy Duty Series

Series: 956 Heavy Duty Series

Questions? Contact Littelfuse Support



Product Literature

 956 Series Ignition Switches 2D Prints

Industries Served

Heavy Duty Truck
Construction
Emergency Vehicles
Bus/Transit
Military
Agriculture



Feedback

Specifications	Technical Resources
Property (Mouseover for details)	Value
Description	Heavy Duty Ignition and Start Switch Heavy Duty Ignition
Number of positions	3
With anti-restart	Start Lockout Feature. Switch Must Go To Off Position Before The Start Circuit Can Be Re-Energized
Actuator	Key
Positions	Off - Ign/Acc - Start
Spring return to Off	Spring Return to Ign
Terminals	4 screw
Key	Bitted Mixed Codes
O-Ring seal in stem	No
Accessory	30A/12V DC
With harness	No
With key boot	No
Ignition/Run	10A/12V DC
Start	5A/12V DC
Removable key	Key Removeable in Off Position Only
Case material	Plated Steel
Sealed terminal insulator	No
Ground terminal	No
Mounting stem	1 (25.4mm)
Contacts	Bronze
Ignition-proof	SAE J259

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).



- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents