

Cutter - THERMOMARK ROLLMASTER-CUTTER - 0804502

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cutter, for the THERMOMARK ROLLMASTER 300/600, cutter width: 120 mm, suitable for: TML, SK, EML, RM, PMM, WMS, WMS-2 HF, WMS-OT HF, TMT continuous media, and EMT (EX15)R



Your advantages

- ✓ Custom length cuts of continuous markers



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 384801
GTIN	4055626384801
Weight per Piece (excluding packing)	1,800.000 g
Weight per piece (including packing)	1,945.000 g
Custom tariff number	82089000
Country of origin	Germany

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19149290
eCl@ss 11.0	19140620
eCl@ss 4.0	24190103
eCl@ss 4.1	24190103

Cutter - THERMOMARK ROLLMASTER-CUTTER - 0804502

Classifications

eCl@ss

eCl@ss 5.0	19020205
eCl@ss 5.1	19020205
eCl@ss 6.0	19149200
eCl@ss 7.0	19149290
eCl@ss 9.0	19149290

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC001675
ETIM 7.0	EC001675

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43211612
UNSPSC 18.0	43211612
UNSPSC 19.0	43211612
UNSPSC 20.0	43211612
UNSPSC 21.0	43211612