

Product data sheet

Specifications



APC Performance SurgeArrest 11 Outlet with Phone (Splitter) and Coax Protection, 120V

P11VT3

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable Length	2.44 m
Number Of Cables	1
Provided Equipment	Coaxial cable Telephone cable User manual

Physical

Colour	Black
Height	4 cm
Width	11.9 cm
Depth	30.2 cm
Net Weight	1.06 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Network Frequency	50/60 Hz
Switching Current Capacity	15 A

Output

Number Of Power Socket Outlets	11
Outlet Standard	NEMA 5-15R

Conformance

UI 1449 Tvss Rating	L-N: 400 L-G: 500 N-G: 500
Product Certifications	CSA
Standards	UL 1363 UL 1449

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Equipment Protection Policy	Lifetime : \$100000
-----------------------------	---------------------

Environmental

Ambient Air Temperature For Operation	-15...45 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

Surge Protection and Filtering

Data Line Protected	1-4
Response Time	1 ns common mode
Common Mode Rejection	70 dB
Surge Energy Rate	3020 J
Data Line Protection	RJ11 analog phone line for phone/fax/modem/DSL Coaxial cable for CATV/SATV/modem/audio-video

Packing Units

Package 1 Height	6 cm
Package 1 Width	19.2 cm
Package 1 Length	34.5 cm
Package 1 Weight	1.35 kg
Number Of Units In Package 2	6
Package 2 Height	381.00 mm
Package 2 Width	203.20 mm
Package 2 Length	381.00 mm
Package 2 Weight	8.88 kg
Scc14	10731304249037

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. **Green Premium** promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low- products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information