GMA.1B.045.DG

Standard



Image for illustrative purpose only

Summary

Request a quote

BKT series

Jacket cable outside diameter [mm]	4.50 - 4.90 mm
Size	1B
Series	B - Indoor keyed


https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-045-dg.html
LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Downloaded from Arrow.com.

Technical details

Form & Material	
Shell style / Model id	GMA - Bend relief Grey
Housing material	Thermoplastic polyurethane
Keying	No keying
Colour	Grey
Weight	0.81 g
Environment	
Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-40°C / +80°C
Cable fixation	
Jacket cable outside diameter [mm]	4.50 - 4.90 mm

Drawings



No keying

Dimensions

	A	L
mm.	4.5	30
in.	0.18	1.18

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-045-dg.html
LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Downloaded from Arrow.com.