



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.


LUG SIDE
(MOMENTARY POSITION)



CENTER
(MAINTAINED POSITION)




OPPOSITE LUG
(MAINTAINED POSITION)



ELECTRICAL DATA


L192 10A 125, 250, 277 VAC
1/4HP 125 VAC,
1/2HP 250, 277 VAC
3A 125 VAC "L"



NOTES

- 1 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING
STAMPED ON SIDE OF SWITCH
- 2 - SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
- ③ - SCREWS FURNISHED UNASSEMBLED

[illegible]

THIRD ANGLE PROJECTION			
			
SCALE FULL			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS CONVERSIONS ARE FOR REFERENCE UNLESS NOTED TOLERANCES ARE $\pm$			
NO PLACES ONE PLACE TWO PLACES THREE PLACES ANGLES	DIM. mm X X, X X, X, X	TOL. mm/in 1/64 0.4/0.16 0.15/1/64	DIM. in X X X X X
			TOL. mm/in 0.8/0.3 0.36/0.015 0.13/0.005
DESIGN UNITS		S: ☐ METRIC	US: ☐ CUSTOMARY
WEIGHT .13 LB EST			